



Pass and Seymour
PlugTail® Commercial Specification Grade 20A USB Charging Receptacles, Black
 Part No. PTTR20ACUSBBK



PlugTail Commercial Specification Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices: one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides ample power needed for charging mobile phones and tablets. The PlugTail termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects

Efficient, 15.5W power supply for fast charging of mobile phones and tablets

Triple-wipe, brass line contacts for 20A commercial applications

Multiple color options available

Zinc-plated steel for corrosion resistance

5Vdc Type-C USB port to charge USB Type-C compatible mobile devices

PlugTail termination allows for more productive, finger-safe installation and added future flexibility

Stainless steel auto-ground clips assure positive ground

Available in 15 & 20A, Specification Grade and Hospital Grade configurations

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007113266	Country Of Origin	China

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----