



Pass and Seymour  
**PlugTail® 20A 125V Hospital-Grade USB Type A/C Outlet, Red**  
 Part No. PTTR20HACUSBRED



PlugTail® Hospital Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices: one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides the power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects

Triple-wipe, brass line contacts for 20A commercial applications

Zinc-plated steel for corrosion resistance

Stainless steel auto-ground clips assure positive ground

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Multiple color options available

5Vdc Type-C USB port to charge USB Type-C compatible mobile devices

Available in 15 & 20A, Specification Grade and Hospital Grade configurations

## Specifications

### General Info

|                   |                                |                       |                                  |
|-------------------|--------------------------------|-----------------------|----------------------------------|
| Product Line      | Pass & Seymour                 | Color                 | Red                              |
| Country Of Origin | China                          | Number of Receptacles | 2                                |
| Features          | USB-A Charging, USB-C Charging | Outlet Type           | Commercial, Indoor, USB-Charging |
| Type              | Outlet                         |                       |                                  |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.693 in | Product Depth US | 1.45 in |
| Product Height US | 2.677 in |                  |         |

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed      Yes

---

## Technical Information

---

|                  |             |                |        |
|------------------|-------------|----------------|--------|
| USB Amperage     | 3.1 A       | Number of USBs | 2      |
| USB Power Output | 15 W        | Amperage       | 20 A   |
| Number of Poles  | Double Pole | Indoor/Outdoor | Indoor |
| Voltage          | 125 V       |                |        |

---