



Pass and Seymour  
**PlugTail® 15A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Brown**  
Part No. PTTR26262



PlugTail® Tamper-Resistant Decorator Spec Grade Receptacle, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007001525	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
Product Height US	2.75 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Is Tamper-Resistant	Yes	Phase	Three
---------------------	-----	-------	-------

---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Indoor/Outdoor	Indoor
----------------	--------

---