



Pass and Seymour
PlugTail® 15A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Black
Part No. PTTR26262BK



PlugTail® Tamper-Resistant Decorator Spec Grade Receptacle, 15A, 125V
PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

Specifications

General Info

| | | | |
|-----------------------|-------------------------|-------------------|--------------------------------------|
| Product Line | Pass & Seymour | Color | Black |
| Finish | Matte | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Commercial, Indoor, Tamper-Resistant |
| Application Sector | Residential/Commercial | Standard | UL 498 |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.875 in |
|------------------|--------|------------------|----------|

| | |
|-------------------|---------|
| Product Height US | 2.75 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|-----|----------|------|
| Is Tamper-Resistant | Yes | Amperage | 15 A |
|---------------------|-----|----------|------|

| | | | |
|-----------------|-------------|----------------|--------|
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
|-----------------|-------------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
