



PlugTail® Tamper-Resistant Decorator Spec Grade Receptacle, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

| | |
|--|--|
| .036 inch thick, brass, triple-wipe power contacts for lasting retention. | No exposed terminals create a finger safe application before, during, and after installation. |
| Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. | Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. |
| Crimped and welded contacts. | Pre-stripped connector leads fasten to conductors, easier than standard pigtailed. |
| Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications. | Auto-ground clip assures positive ground. |

Specifications

General Info

| | | | |
|-------------------|------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | UPC Number | 785007001341 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Tamper-Resistant | Application Sector | Commercial |
| Standard | UL 498, FEDSPEC | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.875 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|-----|-------|-------|
| Is Tamper-Resistant | Yes | Phase | Three |
|---------------------|-----|-------|-------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | |
|----------------|--------|
| Indoor/Outdoor | Indoor |
|----------------|--------|
