



Pass and Seymour
PlugTail® 20A 125V Hospital-Grade Tamper-Resistant Decorator Duplex Receptacle, Gray
 Part No. PTTR26362HGGRY



PlugTail® Tamper-Resistant Hospital Grade Decorator Receptacle, 20A 125V. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects
 - Plated steel wrap strap design for maximum durability and corrosion resistance.
 - Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
 - No exposed terminals create a finger safe application before, during, and after installation.
 - Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
 - For covering patents, see www.legrand.us/patents.
 - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
 - Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Type	Outlet

Dimensions

Product Width US 1.5 in

Product Depth US 0.875 in

Product Height US 2.75 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage 20 A

Number of Poles Double Pole

Indoor/Outdoor Indoor

Voltage 125.0 V
