



Pass and Seymour
PlugTail® Tamper-Resistant Surge Protective Duplex Receptacle, Gray
Part No. PTTR5362GRYSP



PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

For covering patents, see www.legrand.us/patents.

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL

Dimensions

Product Width US	1.7 in	Product Depth US	1.4 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Phase	Single	Frequency Rating	60 Hz
Connection	Built-In Connector	Class	IG
Amperage	20 A	Type of Indicators	LED, Audible Alarm
Voltage	125.0 V	Environmental Conditions	UL94 V2
