



PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

For covering patents, see www.legrand.us/patents.

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007019902
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL		

Dimensions

Product Width US	1.7 in	Product Depth US	1.4 in
------------------	--------	------------------	--------

Product Height US 2.75 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Phase	Single	Connection	Built-in Connector
Class	IG	Amperage	20 A
Type of Indicators	Audible Alarm, LED	Environmental Conditions	UL94 V2