



PlugTail® Tamper-Resistant Split Circuit Spec Grade Duplex Receptacle, 20amp 125volt, Light Almond

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR5362LA
Country Of Origin	Mexico		

### Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Is Tamper-Resistant

Yes

Amperage

20 A

---