



Pass and Seymour  
**PlugTail® Extra Heavy Duty Hospital Grade Tamper-Resistant Receptacles, 15A, 125V, Ivory**  
Part No. PTTR62HI



PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Receptacles, 15A, 125A

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007860498	Country Of Origin	United States
Application Sector	Commercial	Standard	UL 498, FEDSPEC

### Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
------------------	--------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Phase	Three
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG