



Pass and Seymour

PlugTail® Industrial Extra Heavy Duty Spec Grade Tamper-Resistant Receptacles, 15A, 125V, Ivory

Part No. PTTR62I



PlugTail® Industrial Extra Heavy-Duty Spec Grade Tamper-Resistant Receptacles, 15A, 125A

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498		

### Dimensions

---

Product Width US	1.625 in	Product Depth US	0.866 in
------------------	----------	------------------	----------

---

Product Height US	2.75 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	Phase	3
---------------------	-----	-------	---

---

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

---

Voltage	125.0 V
---------	---------

---