



Pass and Seymour
PlugTail® Extra Heavy Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125V, Black
 Part No. PTTR63HBK



PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007860542	Country Of Origin	United States
Application Sector	Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	3	Number of Wires	3
Number of Poles	Double Pole	Wire Size	10-14Awg
Voltage	125 V		
