



Pass and Seymour
PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125V, Red
Part No. PTTR63HRED



PlugTail Extra Heavy-Duty Hospital Grade Tamper-Resistant Duplex Receptacle 20amp 125volt Brown For detailed PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Red	UPC Number	785007860597
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	cULus UL498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Dielectric Strength	Withstands 2000V minimum	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Wire Size	PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only	Number of Wires	3
Environmental Conditions	Flammability: UL94 V2		
