



PlugTail Tamper-Resistant Hospital Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, Brown
 For detailed PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007013412	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	3	Number of Wires	3
Number of Poles	Double Pole	Wire Size	10-14Awg
Voltage	125 V		
