



Pass and Seymour  
**PlugTail® Commercial Passive Infrared (PIR) Wall Switch Sensor, Ivory**  
 Part No. PTWSP250I



Commercial Occupancy Sensor (PIR) PlugTail Automatic Wall Switch with 3 Wire Technology. Compact decorator design, shallow 1\'' back body, positive detection indicator with no minimum load requirement. Available in Ivory, White, Gray and Light Almond. information, visit our PlugTail Headquarters.

## Features & Benefits

- Detection Signature Analysis provides high immunity to RFI and EMI. Integrated light level sensor works from 10 to 150 footcandles.
- Compatible with all electronic and magnetic ballasts, PL lamp balasts, compact fluorescent. Adjustable time delay of 30 seconds to 30 minutes.
- Dual 120/277VAC operation, Adjustable sensitivity from 20% to 100%, 180 degree coverage of up to 900 sq. ft. Patented voltage drop protection and zero crossing circuitry.
- No exposed terminals create a fingersafe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents). :

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007016970	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	CSA Listed, cULus, UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

---

Target Size	180°	Response Frequency	60 Hz
Sensing Range	900 sq ft	Sensitivity	60Hz
Load	120/277VAC	Environmental Conditions	Indoor Use Only

---