



On-Q
12VDC, 30W Power Supply
Part No. PW7725

Powers connected home devices by converting high voltage alternating current (AC) to low voltage direct current (DC)



Features & Benefits

Package includes a DC power supply with 2 ft barrel connector plug and 1.5 ft AC power plug IEC C13/C14 connections
Stacks neatly in enclosure with AC1031 power strip

Specifications

General Info

UPC Number	804428028475	Country Of Origin	China
Product Line	On-Q	Application Sector	Residential
Standard	UL, cULus, CE, FCC, C-Tick, RoHS		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Input Voltage	100 to 240 (50/60Hz)	Connection	DC Barrel
---------------	----------------------	------------	-----------

Environmental Conditions	10 to 90 (relative humidity, non-condensing)	Output Voltage	12 V
--------------------------	--	----------------	------
