



On-Q
12VDC, 18W Power Supply
Part No. PW7760

Powers connected home devices by converting high voltage alternating current (AC) to low voltage direct current (DC)



Features & Benefits

Package includes a DC power supply with 2 ft barrel connector plug and a 1.5 ft AC power plug

IEC C7/C8 connections (‘figure 8’)

Stacks neatly in enclosure with AC1031 power strip

Specifications

General Info

UPC Number	804428037453	Country Of Origin	China
Product Line	On-Q	Application Sector	Residential
Standard	UL, cULus, FCC, RoHS		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Input Voltage	100 to 240 (50/60Hz)	Connection	DC Barrel
Environmental Conditions	85 (relative humidity, non-condensing)	Output Voltage	12 V