



Cisco QSFP-40G-SWDM4 Compatible 40GBase-SWDM4 QSFP+ Transceiver (MMF, 850nm-940nm, 400m, LC Duplex, DDM, C-Temp)



Features & Benefits

Guaranteed Compatible
In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty
For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate
Extensive inventory guarantees same day shipping.

99.98% Reliability Rate
Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty
For more information by product line, visit our Warranty page.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	Malaysia
Warranty Type	Lifetime	Type	Transceiver

Dimensions

Product Width US	18.35 mm	Product Depth US	121.9 mm
Product Height US	8.5 mm		

Technical Information

Fiber Optic Cable Type	Multimode	Operating Temperature Min	0 C
Operating Temperature Max	70 C	Connector Type	LC Duplex
Wavelength	850nm		