

This Cisco® QSFP-100G-SR4-S Compatible QSFP28 transceiver provides 100GBase-SR throughput up to 100m over multi-mode fiber (MMF) at a wavelength of 850nm using a MPO connector. It is guaranteed to be 100% compatible with the equivalent Cisco® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

| | |
|---|---------------------------------------|
| Distance Ranging from 100M to 40km (with FEC) | QSFP28 MSA Compliant |
| Dual Rate Operation of 103 and 112Gbps | IEEE 802.3ba LWDM Wavelengths |
| Includes Digital Optical Monitoring (DOM) | Commercial Temperature Range |
| TAA & BAA Compliant | 1270nm to 1330nm wavelength signaling |

Specifications

General Info

| | | | |
|--------------|--------------|-------------------|---------------|
| UPC Number | 757120667384 | Country Of Origin | United States |
| Product Line | Legrand | | |
