



RFI Rotary Dimmer 1000W, Ivory

## Features & Benefits

- Slimmer design -- the trimmest rotary dimmers, 1/4 in. less depth than the leading competitor's models.
- Easy-to-grip knob with soft, contemporary curves goes with any color. Interchangeable with older-style knobs.
- Excellent RFI/EMI filtering performance -- won't impact sensitive electronic devices.
- Pre-stripped leads speed termination.
- No de-rating of 600 watt models in multi-gang applications. Leaves more room in the box for faster, easier installation.
- Makes small adjustments in lighting levels easier.
- Illuminated models are easy to find in the dark.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	R600IV
Color	Ivory	Country Of Origin	China
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

### Technical Information

Operating Cycles	100000	Actuator	Touch
------------------	--------	----------	-------

---

Number of Poles	Single Pole	Wattage	1000 W
Voltage	120.0 V	Load	1000 Watt

---