



RFI Rotary Dimmer, 1000w Preset 3way, Light Almond

Features & Benefits

Slimmer design -- the trimmest rotary dimmers, 1/4 in. less depth than the leading competitor's models. Easy-to-grip knob with soft, contemporary curves goes with any color. Interchangeable with older-style knobs.

Excellent RFI/EMI filtering performance -- won't impact sensitive electronic devices. Pre-stripped leads speed termination.

No de-rating of 600 watt models in multi-gang applications. Leaves more room in the box for faster, easier installation.

Makes small adjustments in lighting levels easier. Illuminated models are easy to find in the dark.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	R603PLAV
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Operating Cycles	100000	Actuator	Touch
Number of Poles	Single Pole	Wattage	1000 W

Voltage

120.0 V

Load

1000 Watt
