



## radiant Collection

radiant® 15A Tamper-Resistant Ultra-Fast USB Type-A/C Outlet  
Part No. R26USBAC6BK



Charge phones, tablets and more up to 40% faster, with Ultra-Fast USB Outlets from the radiant® Collection. With an industry-leading 27W of power supplying the included USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, the Ultra-Fast updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

### Features & Benefits

- Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter. Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.
- Includes connections for both traditional USB Type-A and the newer USB Type-C, to accommodate all mobile devices. All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect. Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.
- More color options available to fit any style, including finishes to match current hardware and lighting trends. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

### Specifications

#### General Info

Color	Black	UPC Number	785007207521
Country Of Origin	China	Product Line	Pass & Seymour

#### Dimensions

Product Width US	1.69 in	Product Height US	4.18 in
Product Depth US	1.35 in		

#### Technical Information

Voltage	125 V	Mounting Type	Box
---------	-------	---------------	-----