



radiant Collection
radiant® 15W USB Outlet, Type A/C, 15A, Tamper-Resistant, Dark Bronze
Part No. R26USBAC6DBCCV4



Charge phones, tablets and more up to 40% faster, with USB Outlets from the radiant® Collection. With an industry-leading 27W of power supplying the included USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, this USB updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Includes connections for both traditional USB Type-A and the newer USB Type-C , to accommodate all mobile devices.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Dark Bronze
Finish	Metallic	UPC Number	785007207583
Country Of Origin	Vietnam	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Residential	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.693 in	Product Depth US	1.35 in
Product Height US	4.18 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	6 A
Number of USBs	2	USB Power Output	15 W
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Mounting Type	Box
Environmental Conditions	95% (relative humidity, non-condensing)		