



radiant Collection  
radiant® 15A Tamper-Resistant Ultra-Fast USB Type A/C Outlet, White  
Part No. R26USBAC6W



Charge phones, tablets and more up to 40% faster, with Ultra-Fast USB Outlets from the radiant® Collection. With an industry-leading 27W of power supplying the included USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, the Ultra-Fast updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Includes connections for both traditional USB Type-A and the newer USB Type-C , to accommodate all mobile devices.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                       |   |                   |                                |
|-----------------------|---|-------------------|--------------------------------|
| Product Line          | Pass & Seymour                                      | Color             | White                          |
| Finish                | Matte   | Country Of Origin | Vietnam                        |
| Number of Receptacles | 2   | Features          | USB-A Charging, USB-C Charging |
| Outlet Type           | Indoor, Residential, Tamper-Resistant, USB-Charging | Warranty Type     | 1-Year Limited Warranty        |
| Type                  | Outlet  |                   |                                |

Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.693 in | Product Depth US | 1.35 in |
| Product Height US | 4.18 in  |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                          |   |                         |             |
|--------------------------|---|-------------------------|-------------|
| Is Tamper-Resistant      | Yes                                     | USB Amperage            | 6 A         |
| Number of USBs           | 2                                       | USB Power Output        | 15 W        |
| Amperage                 | 15 A                                    | Number of Poles         | Double Pole |
| Indoor/Outdoor           | Indoor                                  | NEMA Configuration Code | 5-15R       |
| Mounting Type            | Box                                     | Voltage                 | 125.0 V     |
| Environmental Conditions | 95% (relative humidity, non-condensing) |                         |             |