



radiant Collection
radiant® 15A Tamper-Resistant USB Type A/C Outlet, Ivory
Part No. R26USBACICCV4



Make it easier to get a full battery for your smartphones, tablets and more with the convenience of built-in charging. A perfect charging solution for your current and future electronic devices, this tamper-resistant USB outlet features connections for USB Type-A and the newer USB Type-C. Easily replacing traditional outlets in as little as ten minutes, this outlet offers accessible charging without needing bulky adapters or sacrificing your plugs, and features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Accommodates all mobile devices with connections for both traditional USB Type-A and the newer USB Type-C, which features a smaller, reversible connector and high-speed specs.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Replaces a traditional outlet easily, in as little as 10 minutes.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Indoor, Residential, Tamper-Resistant, USB-Charging
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.35 in
------------------	----------	------------------	---------

Product Height US 4.18 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	3.1 A
---------------------	-----	--------------	-------

Number of USBs	2	USB Power Output	15 W
----------------	---	------------------	------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

Voltage	125.0 V
---------	---------
