



radiant Collection
radiant® 15W USB Outlet, Type C, 15A, Tamper-Resistant, White
Part No. R26USBC6WPWCCV4



Charge phones, tablets and more up to 40% faster, with USB Outlets from the radiant® Collection. With an industry-leading 30W of power supplying its two included USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, the USB updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Accommodates the latest mobile devices with two USB Type-C connections.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007207811	Country Of Origin	China
Number of Receptacles	2	Features	USB-C Charging
Outlet Type	Tamper-Resistant, USB-Charging	Application Sector	Hospitality, Multi-Dwelling Unit, Residential
Wall Plate Included	Yes	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

Dimensions

Product Width US	1.693 in	Product Depth US	1.35 in
Product Height US	4.18 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
USB Wattage	15 W	USB Amperage	6 A
Number of USBs	2	Number of Wires	3
USB Power Output	15 W	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Mounting Type	Box	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	5.0 V		