



Pass and Seymour
Rotary R Series Dimmer, Ivory
Part No. R600PIV



RFI Rotary Dimmer Preset 660W, White

Features & Benefits

- Slimmer design -- the trimmest rotary dimmers, 1/4 in. less depth than the leading competitor's models.
- Excellent RFI/EMI filtering performance -- won't impact sensitive electronic devices.
- No de-rating of 600 watt models in multi-gang applications.
- Makes small adjustments in lighting levels easier.
- For covering patents, see www.legrand.us/patents.
- Easy-to-grip knob with soft, contemporary curves goes with any d. cor. Interchangeable with older-style knobs.
- Pre-stripped leads speed termination.
- Leaves more room in the box for faster, easier installation.
- Illuminated models are easy to find in the dark.

Specifications

General Info

Color	Ivory	UPC Number	785007045697
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Type	Dimmer
Standard	UL listed		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	95219
--------------	-----	---------------------	-------

Technical Information

Wattage	600 W	Number of Poles	Single Pole
Voltage	120 V	Load	600Watt