




Wiremold
Plug-In Outlet Center Unit / Rack Mount 120V/15A/8 rear O/L /lighted switch/6' cord/Computer Grade Surge
Part No. R8BZ



Eight rear outlets, lighted switch, 15A. Receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 6' (1.8m) cord. Perma Power computer grade surge protection.

Features & Benefits

Eight rear outlets, lighted switch, 15A. Receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 6' (1.8m) cord. Perma Power computer grade surge protection.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776012200
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	cULus Recognized: File E66421: Guide XBYS2, XUHT2, VZCA12	Type	PIOC

Dimensions

Product Width US	19.0 in	Product Height US	2.57 in
Product Length US	1.75 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single Stage	Frequency Rating	+35dB Hz
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Mounting Type	Rack Mounting
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V		