



Wiremold
RC3 Multi-Service Poke-Thru Assembly, Gray
Part No. RC3ATCGY



Assembled unit. Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground. Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS). Slide covers match the painted flange colors: gray, black, and ivory. Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum colored slide holder (AA). Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Specifications

General Info

Color	Gray	UPC Number	786564067009
Country Of Origin	Mexico	Product Line	Wiremold
Application Sector	Commercial	Type	Poke-Thru
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21, 300.22[C] & 314 of NEC.	Number of Knockouts	2

Dimensions

Product Volume US	900.0 cu in	Product Width US	7.5 in
Product Height US	7.5 in	Product Weight US	4.82 lb
Product Depth US	16.0 in	Core Hole Size	4 in
Cubic Capacity	24.5 cu in		

Listing Agencies / 3rd Party Agencies

cULus Listed

Yes

cULus ListingNumber

E2961

Buy American Act Compliance

NAFTA

Yes

Additional Information

RoHS Conformant

Yes

Product Environmental Profile

Yes

Technical Information

Number of Outlets

2
