



Prewired 15A quad receptacle can be wired as standard quad receptacle or isolated ground. Flange available painted in gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS). Aluminum and brass flanges shipped with black cover. Brass flange also available with brass colored cover assembly (AB). Aluminum flange also available with aluminum colored cover assembly (AA). RC9 Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

## Specifications

### General Info

UPC Number	786564005544	Country Of Origin	Mexico
Product Line	Wiremold	Application Sector	Commercial
Type	Poke-Thru	Construction	Assembled
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21, 300.22[C] & 314 of NEC.	Number of Knockouts	2

### Dimensions

Cubic Capacity	24.5 cu in
----------------	------------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	E2961
--------------	-----	---------------------	-------

### Buy American Act Compliance

NAFTA	Yes
-------	-----

### Additional Information

---

RoHS Conformant    Yes

Product Environmental Profile    Yes

---

## Technical Information

---

Number of Outlets    4

---