



All communication device accepts up to four UTP connectors. Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS). Aluminum and brass flanges shipped with black cover. Brass flange also available with brass colored cover assembly (AB). Aluminum flange also available with aluminum colored cover assembly (AA). Unit includes two (2) Ortronics TracJack adapters, two (2) Ortronics Series II adapters, and two (2) Wiremold Open System adapters. Modular jacks sold separately. NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters. RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

| | |
|--|--|
| All communication device accepts up to four UTP connectors | Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS) |
| Aluminum and brass flanges shipped with black cover | Brass flange also available with brass colored cover assembly (AB) |
| Aluminum flange also available with aluminum colored cover assembly (AA) | Modular jacks sold separately |
| Modular jacks sold separately | NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters |
| RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole | Not designed to work with bare concrete or terrazzo |
| Floor covering thickness 1/8" minimum | RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole |

Specifications

General Info

| | | | |
|---------------------|--------------------------------|--------------------|--|
| Product Line | Wiremold | Color | Black |
| UPC Number | 786564006558 | Country Of Origin | Mexico |
| Construction | Assembled | Cover Style | Surface |
| Number of Knockouts | 1 | Application Sector | Commercial, Education, Healthcare, Hospitality |
| Standard | UL Fire Classified, cULus, NEC | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |

| | | | |
|---------------------------------------|--------------|-------------------|----------|
| Type | Poke-Thru | | |
| Dimensions | | | |
| Product Width US | 7.0 in | Product Weight US | 2.981 lb |
| Product Height US | 10.0 in | Core Hole Size | 3 in |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | E2961 | cULus Listed | Yes |
| Additional Information | | | |
| RoHS Compliant | Yes | | |
| Technical Information | | | |
| Floor Type | Carpet, Tile | Service Capacity | Dual |
| Fire Rating | 2 hr | Cable Entry | Conduit |