



radiant Collection
radiant® Two Single-Pole Switches, Ivory
Part No. RCD11I



Control two separate lights or devices from a single location with this combination switch. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection.
- Features durable, high-impact resistant thermoplastic construction.
- Designed to install easily with a narrower back body and captivated mounting screws.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Features	Combination, Locator Light
Switch Type	Push	Number of Switches	2
Application Sector	Residential	Standard	cULus, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.81 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Contact Configuration	15A	Operating Cycles	50000
Contact Rating	120	Number of Gangs	1
Amperage	15 A	Number of Poles	Single Pole
Mounting Type	Box	Voltage	125.0 V
Environmental Conditions	UL94 V2		