



radiant Collection  
radiant® Two Single Pole/3-Way Switches, Nickel  
Part No. RCD33NICC6



Control two separate lights or devices from a single location with this combination switch. Both switches feature installation flexibility, usable for single-pole or 3-way applications. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

### Features & Benefits

- Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection.
- Features durable, high-impact resistant thermoplastic construction.
- Designed to install easily with a narrower back body and captivated mounting screws.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Nickel
Country Of Origin	China	Features	Combination, Locator Light
Switch Type	Push	Number of Switches	2
Warranty Type	1-Year Limited Warranty	Type	Switch

#### Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.81 in		

Listing Agencies / 3rd Party Agencies

cULus Listed                      Yes

Technical Information

Number of Gangs                      1    Amperage                      15 A

Number of Poles                      3-Way, Single Pole                      Mounting Type                      Box

Voltage                      120.0 V