



radiant Collection
radiant® Single Pole/3-Way Switch with 15A Tamper-Resistant Outlet, Gray
Part No. RCD38TRGRY



A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces a standard switch/outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style.

Offers installation flexibility, working in both single-pole and 3-way applications.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|---|-----------------------|------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007233582 |
| Country Of Origin | China | Number of Receptacles | 1 |
| Features | Combination, Locator Light | Switch Type | Push |
| Number of Switches | 1 | Outlet Type | Tamper-Resistant |
| Application Sector | Hospitality, Multi-Dwelling Unit, Residential | Wall Plate Included | No |
| Warranty Type | 1-Year Limited Warranty | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.29 in | Product Depth US | 1.59 in |
| Product Height US | 3.81 in | | |

Technical Information

| | | | |
|---------------------|---------------|----------------------|--------------------|
| Is Tamper-Resistant | Yes | Connection Location | Back and Side |
| Number of Wires | 5 | Number of Gangs | 1 |
| Amperage | 15 A | Number of Poles | 3-Way, Single Pole |
| Wire Size | #14 - #10 AWG | Indoor/Outdoor | Indoor |
| Mounting Type | Box | Wire Connection Type | Screw Terminals |
| Voltage | 120/125 V | | |