



radiant Collection
radiant® FPC 2OL NICKEL 10FT CORD
Part No. RD2RNI10



radiant Furniture Power Centers bring a sleek, modern design and traditional power together. Quick and easy installation means nearly every piece of furniture can be powered up and ready to recharge devices. A sleek design and tamper-resistant receptacles bring your furniture a step above ordinary.

Features & Benefits

Simply cut an opening, insert, tighten clamps, snap on the bezel and plug in.

Specifications

General Info

| | | | |
|-----------------------|--|-------------------|----------------------------|
| Product Line | Wiremold | Color | Nickel |
| UPC Number | 786776192650 | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | Tamper-Resistant |
| Application Sector | Commercial Office, Education, Hospitality, Multi-Dwelling Unit, Municipal, Retail, Transportation, Worship | Standard | CETLUS Listed: Guide FPDU5 |
| Warranty Type | 1-Year from Installation or 2-Years from Day of Sale | Type | Furniture Power Center |

Dimensions

| | | | |
|------------------|----------|-------------------|---------|
| Product Width US | 4.6 in | Product Weight US | 1.98 lb |
| Product Depth US | 2.125 in | Product Height US | 2.5 in |
| Internal Depth | 2 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-------------------|------------------|
| ETL Listed | Yes | ETL ListingNumber | 103010048BOX-001 |
|------------|-----|-------------------|------------------|

Technical Information

| | | | |
|-------------------------|----------------|---------------|------------|
| Wiring Configuration | Single Circuit | Cord Length | 10 ft |
| Amperage | 15 A | Wiring Method | Cord-ended |
| NEMA Configuration Code | 5-15R | Mounting Type | Recessed |
| Cutout Shape | Rectangular | Voltage | 125.0 V |