



RDC610 Modular Patch Cord, blue, 12', reduced diameter, 28 AWG, cat6a channel four-pair UTP stranded PVC/CM.

Features & Benefits

- Each cord is 100% factory tested: Ensures every cord shipped support Category 6a channel specifications.
- Premium plug designed for reduced OD 28AWG patch cable: Protects performance through the plug termination
- Premium 28AWG conductor cordage: Reliable performance and durable cord life.
- Improved cable flexibility: Supports simple routing and cable management
- Reduced cable diameter: Tighter bend radiuses & occupy less cable management space supporting more airflow
- Snagless plug design: Protects plugs when routing through cable managers or pathways.
- Backwards compatible to Category 6, and 5e: Supports lower category installations and components.

Specifications

General Info

| | | | |
|-------------------|-----------|--------------------|------------------------------|
| Product Line | Ortronics | UPC Number | 662875851813 |
| Country Of Origin | Mexico | Application Sector | Commercial/Industrial |
| Standard | FCC | Type | Reduced Diameter Patch Cords |

Dimensions

| | |
|-------------------|---------|
| Product Length US | 12.0 FT |
|-------------------|---------|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|