




radiant Collection

radiant® Incandescent Pole/3-Way Dimmer
Part No. RH703PTCCCV6



Upgrade your space with superior dimming control and exceptional style. The radiant® Tru-Universal Dimmer works with virtually any 120V dimmable bulb or fixture, adjusting to the precise light level you want, without the flicker. Unsure what dimmer your bulb needs? Avoid uncertainty with Tru-Universal Dimming. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch.

Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any basic switch or dimmer with ease, in both single-pole and 3-way applications. For use with incandescent lighting.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating* required in multi-gang applications. *Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Screw pressure plate back wire allows easier installation and fit into the wall box

For covering patents, see www.legrand.us/patents.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level when turning back on or after a power outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Eliminates the need to derate LED bulbs when in multi-gang situations

Specifications

General Info

Color	White, Ivory, Light Almond	UPC Number	785007053715
Country Of Origin	China	Product Line	Pass & Seymour
Number of Switches	1	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.29 in	Product Height US	3.18 in
Product Depth US	1.0 in		

Technical Information

Wattage	700 W	Number of Poles	Single Pole, 3-Way
Number of Gangs	1	Mounting Type	Box