



radiant Collection  
radiant® Fan Speed Control Switch and De-Hummer, Single-Pole/3-Way, Bi-Color  
Part No. RHDH163PBCCCV4



Upgrade your fan control with the sweet sound of silence. Specially designed to virtually eliminate the fan motor "hum." This device provides quieter fan speed control while featuring the sleek, clean lines of radiant® for a sophisticated touch. This fan control switch handles a max load of 1.6A. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Designed to virtually eliminate the motor's hum for quieter use.

Installs easily in place of a standard light or fan control switch. Rated for a max load of 1.6A.

Offers installation flexibility, working in both single-pole and 3-way applications.

Returns the fan to its previous level after a power failure.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Dark Bronze, Nickel
Finish	Frosted	Country Of Origin	China
Features	Fan Control	Switch Type	Paddle
Number of Switches	1	Warranty Type	Limited Lifetime Warranty

### Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

Technical Information

---

Number of Gangs                      1                                      Amperage                      15 A

---

Number of Poles                      3-Way, Single Pole                      Mounting Type                      Box

---

Voltage                      120.0 V

---