



radiant Collection
radiant® 120V, 1100VA Magnetic Low-Voltage Single Pole/3-Way Dimmer, Tri-Color
Part No. RHLV1103PTC



Upgrade your space with precise dimming control and exceptional style, while saving energy and extending bulb life by reducing the amount of electricity required to power the lights. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.
- Usable in both single-pole and 3-way applications.

Constant memory features returns lights to their previous level after a power failure or outage.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Country Of Origin	China	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Dimensions

Product Width US	2.5 in	Product Depth US	1.25 in
------------------	--------	------------------	---------

Product Height US	4.25 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
------------------	--------------	------------	-----------------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Bulb Compatibility	Halogen	Number of Poles	3-Way, Single Pole
--------------------	---------	-----------------	--------------------

Wattage	1100 W	Mounting Type	Box
---------	--------	---------------	-----

Voltage	120.0 V	Load	Low Voltage
---------	---------	------	-------------

Environmental Conditions	Humidity: Less than 95% non condensing
--------------------------	--