



radiant Collection
radiant® 4-Button Digital Timer, Nickel
Part No. RT2NICCV4



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
UPC Number	785007158380	Country Of Origin	China
Features	Timer	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential/Commercial
Standard	cULus	Warranty Type	5-Year
Type	Switch		

Technical Information

Connection	Back and side wire	Coil Voltage	120 V
Contact Rating	600Watts	Number of Gangs	1
Number of Buttons	4	Amperage	15 A
Number of Poles	Single Pole	Indoor/Outdoor	Indoor
Timing Range	10-60 minutes	Wattage	600 W
Mounting Type	Box		