



Designed to complement any space, the radiant® Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this six-gang option with a combination of radiant® switches, dimmers, and/or outlets for a completed look that's a step above ordinary.

### Features & Benefits

- Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends. Molded of rugged .065" thick polycarbonate
- One-piece subplate mounts over the device for easy retrofit and a lower profile. Subplate screws align devices to ensure proper positioning of the wall plate.
- Opening accommodates all NEMA 26-opening devices. An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.

### Specifications

#### General Info

Color	Nickel	UPC Number	785007295993
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL514, cULus, CSA Certified

#### Dimensions

Product Width US	12.21 in	Product Height US	4.94 in
Product Depth US	0.15 in		

#### Technical Information

Number of Gangs	6	Mounting Type	Screwless
Cutout	Decorator	Thickness	0.065 in