



Features & Benefits

Subplate screws align devices: to ensure proper positioning of the wall plate. An extra 3/8" width and height than standard size wall plates: for more tolerance in covering ragged sheet rock openings.

Opening accommodates all NEMA 26-opening devices.

5048

Molded of rugged .065" thick polycarbonate for greater durability.

One-piece subplate: mounts over the device, allowing you to simply snap on the wall plate with ease.

Specifications

General Info

Color	Nickel	UPC Number	785007320770
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL514 cULus CSA Certifie

Dimensions

Product Width US	4.96 in	Product Height US	4.94 in
Product Depth US	0.15 in		

Technical Information

Number of Gangs	2	Mounting Type	Screwless
Cutout	Decorator	Thickness	0.065 in