



Pass and Seymour  
Old Work Switch and Outlet Box with Quick/Click  
Part No. S116W



Single-Gang, Old Work Switch and Outlet Box with Swing Bracket for mounting. Adjusts from 1 1/4-inch down to 1/8-inch. Two Auto/Clamps on Each End. 100 pack.

## Features & Benefits

Quick/Click feature secures devices quickly and easily.

Does not strip when over-torqued.

2: Auto/Clamps on each end eliminate the need for separate cable clamps.

Metal swing bracket for quick mounting in existing walls.

Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

Durable, impact-resistant thermoplastic box.

## Specifications

### General Info

|              |   |                    |                         |
|--------------|---|--------------------|-------------------------|
| Product Line | Pass & Seymour                              | Color              | Gray                    |
| UPC Number   | 785007042504                                | Country Of Origin  | United States           |
| Features     | Auto Clamps, Old Work, Quick Entry, Shallow | Application Sector | Commercial, Residential |
| Standard     | UL Listed                                   | Warranty Type      | 1-Year Limited Warranty |
| Type         | Switch & Outlet Boxes                       |                    |                         |

### Dimensions

|                   |         |                  |                    |
|-------------------|---------|------------------|--------------------|
| Product Width US  | 2.25 in | Product Depth US | 2.75 in            |
| Product Length US | 3.75 in | Cubic Capacity   | 16 in <sup>3</sup> |

### Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

|                 |                   |                |             |
|-----------------|-------------------|----------------|-------------|
| Number of Gangs | 1                 | Indoor/Outdoor | Indoor      |
| Cable Entry     | Back, Bottom, Top | Box Shape      | Rectangular |
| Mounting Type   | Swing Bracket     |                |             |

---