



Pass and Seymour
Screw Mount, Steel Stud Box with Quick/Click
Part No. S118RS



Single-Gang Steel-Stud Box with Quick/Click and Captive Combo Head Self-Tapping Mounting Screws on Each End. Two Quick/Entries on each end. 100 pack.

Features & Benefits

Quick/Entry: feature speeds installation by eliminating need for tools, allows you to push stripped or unstripped non-metallic cable into a single gang plastic box without removing knockouts.

Can be used for steel, aluminum, or wood studs.

Molded of high-impact thermoplastic.

Quick/Click: feature for fast, easy, secure installations. Cannot cross-thread or strip a mounting screw.

Can be installed on steel studs with most standard crimping tools in addition to CT1 Crimping Tool.

Specifications

General Info

| | | | |
|---------------------|--|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007651713 | Country Of Origin | United States |
| Features | Quick Entry, Shallow, Steel Stud Mount | Installation Location | Wall |
| Number of Knockouts | 4 | Application Sector | Commercial, Residential |
| Standard | Residential/Commercial | Warranty Type | 1-Year Limited Warranty |
| Type | Switch & Outlet Boxes | | |

Dimensions

| | |
|----------------|--------------------|
| Cubic Capacity | 18 in ³ |
|----------------|--------------------|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|-----------------|-------------------|----------------|-------------|
| Number of Gangs | 1 | Indoor/Outdoor | Indoor |
| Cable Entry | Back, Bottom, Top | Box Shape | Rectangular |
| Mounting Type | Screw Mount | | |
