



Ceiling Fan Box, Construction Grade with four Auto/Clamps. 30 pack.

## Features & Benefits

- Constructed of impact-resitant Noryl thermoplastic, making it virtually unbreakable and non-conductive.
  - Auto Clamp cable clamps molded in, hold wire securly in box.
  - UL Listed for fan and fixture support.
  - Large, 20.25 cubic inch capacity for extra wiring space.
  - Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.
  - Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.
  - Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.
  - Fan mounts directly to bracket through box with #10-32 screws (provided).
  - Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.
  - Ringed nails for tighter grip.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL listed		

### Dimensions

Cubic Capacity	20.25 cu in
----------------	-------------

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

---

Number of Outlets	1
-------------------	---

---