



Pass and Seymour
4-in Round Ceiling Box
Part No. S120BFAN



Ceiling Fan Box, Construction Grade with four Auto/Clamps. 30 pack.

Features & Benefits

Constructed of impact-resitant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.

Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.

For covering patents, see www.legrand.us/patents.

Auto Clamp cable clamps molded in, hold wire securely in box.

Large, 20.25 cubic inch capacity for extra wiring space.

Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.

Fan mounts directly to bracket through box with #10-32 screws (provided).

Ringed nails for tighter grip.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007206708	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	UL listed

Dimensions

Cubic Capacity	20.25 cu in
----------------	-------------

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Outlets 1
