



4 Round Ceiling Box with a bar hanger that adjusts to 16 or 24 joist spacing. It has four Auto/Clamps. It is constructed with impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive. Its depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling. 50 pack.

Features & Benefits

Auto/Clamp cable clamps molded in, hold wire securely in box.

UL Listed for fixture support, up to 50 pounds.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007206937	Country Of Origin	United States
Features	Auto Clamps, Fixture Rated	Installation Location	Ceiling
Number of Knockouts	4	Application Sector	Commercial, Residential
Standard	UL Listed	Warranty Type	1-Year Limited Warranty
Type	Ceiling Box		

Dimensions

Product Width US	4.0 in	Product Depth US	2.188 in
Cubic Capacity	20.25 in ³		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Indoor/Outdoor	Indoor	Cable Entry	Back, Side
Box Shape	Round	Mounting Type	Stud Mount
