



4-inch Round Ceiling Box with J-Bracket, Two captive Mounting Nails and Four Auto/Clamps. 50 pack.

## Features & Benefits

Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

: Auto/Clamp cable clamps molded in, hold wire securely in box.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

## Specifications

### General Info

|                     |  |                       |                         |
|---------------------|--|-----------------------|-------------------------|
| Product Line        | Pass & Seymour   | Color                 | Black                   |
| UPC Number          | 785007206951   | Country Of Origin     | United States           |
| Features            | Auto Clamps, Dual Threaded Mounting Holes, Fixture Rated | Installation Location | Ceiling                 |
| Number of Knockouts | 4  | Application Sector    | Commercial, Residential |
| Standard            | UL listed  | Warranty Type         | 1-Year Limited Warranty |
| Type                | Ceiling Box  |                       |                         |

### Dimensions

|                |                       |
|----------------|-----------------------|
| Cubic Capacity | 20.25 in <sup>3</sup> |
|----------------|-----------------------|

### Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

|                   |        |               |            |
|-------------------|--------|---------------|------------|
| Indoor/Outdoor    | Indoor | Cable Entry   | Back, Side |
| Box Shape         | Round  | Mounting Type | Stud Mount |
| Number of Outlets | 1      |               |            |

---