



Ceiling Fan Box, Premium Grade with integral fan mounting bracket and four Auto/Clamps. 12 pack.

## Features & Benefits

Constructed of impact-resitant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

Auto Clamp cable clamps molded in, hold wire securly in box.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.

Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.

Fan mounts directly to bracket through box with #10-32 screws (provided).

Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.

Ringed nails for tighter grip.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007652710	Country Of Origin	United States
Features	Auto Clamps, Fan Rated, Fixture Rated, Integral Bracket, Threaded Mounting Holes	Installation Location	Ceiling
Number of Knockouts	4	Application Sector	Commercial, Residential
Standard	UL Listed	Warranty Type	1-Year Limited Warranty

Type	Ceiling Box		
Dimensions			
Product Width US	4.0 in	Product Depth US	2.188 in
Cubic Capacity	20.25 in³		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Indoor/Outdoor	Indoor	Cable Entry	Back, Side
Box Shape	Round	Mounting Type	Stud Mount