



Pass and Seymour  
4-inch Round Ceiling Box  
Part No. S120RAC



4\\ Round Ceiling Box with two captive mounting nails and four Auto/Clamps. It is constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive. Its depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling. 50 pack.

## Features & Benefits

Auto/Clamp cable clamps molded in, hold wire securely in box.

UL Listed for fixture support.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007206975	Country Of Origin	United States
Features	Auto Clamps, Dual Threaded Mounting Holes, Fixture Rated	Installation Location	Ceiling
Number of Knockouts	4	Application Sector	Commercial, Residential
Standard	UL Listed	Warranty Type	1-Year Limited Warranty
Type	Ceiling Box		

### Dimensions

Product Width US	4.0 in	Product Depth US	2.188 in
Cubic Capacity	20.25 in <sup>3</sup>		

---

**Additional Information**

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

**Technical Information**

---

Indoor/Outdoor	Indoor	Cable Entry	Back, Side
----------------	--------	-------------	------------

---

Box Shape	Round	Mounting Type	Stud Mount
-----------	-------	---------------	------------

---